

Double Pole, Double Throw Switch, 15 amps, 120/277 volts, Brown.



Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Fiber terminal insulation barriers standard.

Bodies, covers, and toggles molded of durable nylon.

Locking Switches supplied with one 1498-NT key.

For covering patents, see www.legrand.us/patents.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Single Pole-Double Throw and Double Pole-Double Throw.

Normally open.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Color Brown

UPC Number 785007122206

Country Of Origin Mexico

Product Line Pass & Seymour

Standard UL Listed

Listing Agencies / 3rd Party Agencies

CSA Listed Yes

CSA File Number 17949

Technical Information

Wattage 2 W

Number of Poles Double Pole

Voltage 120 VAC
