



Pass and Seymour  
Heavy Duty Momentary Toggle Switch, Gray  
Part No. 1250-GRY



Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating. Tested to 3 Amps, 24Vdc rating.

## Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw and Double Pole-Double Throw.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Wattstopper	Color	Gray
UPC Number	754182928156	Country Of Origin	China

### Dimensions

Product Width US	2.0 in	Product Weight US	0.24 lb
Product Volume US	27.0 cu in	Product Depth US	4.5 in
Product Height US	2.4 in		

---

Technical Information

---

Amperage	15 A
----------	------

---