



Pass and Seymour
Hospital Grade 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Gray
Part No. 1597HGGRY



Hospital-Grade 15A Self-Test Duplex GFCI

Features & Benefits

Hospital Grade Self-Test GFCI

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	China	Application Sector	Residential/Commercial
Standard	cULus, UL Listed, FSUL		

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Interrupt Rating	4 A	Frequency Rating	60 Hz
Trip Range	5±1 mA	Connection	Back and Side Wire
Amperage	15 A	Number of Poles	Double Pole
Voltage	125.0 V	Environmental Conditions	95% Humidity, UL 94 V2