



Pass and Seymour

Hospital Grade Isolated Ground Tamper-Resistant 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Orange

Part No. 1597IGHGTRO



Hospital-Grade Isolated Ground Tamper-Resistant 15A Self-Test Duplex GFCI

Features & Benefits

Hospital Grade Tamper Resistant GFCI

Specifications

General Info

| | | | |
|-------------------|------------------------|--------------------|------------------------|
| Product Line | Pass & Seymour | Color | Orange |
| Country Of Origin | China | Application Sector | Residential/Commercial |
| Standard | cULus, UL Listed, FSUL | | |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.73 in | Product Depth US | 1.03 in |
| Product Height US | 4.2 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|---------------------|--------------------|------------------|-----------|
| Is Tamper-Resistant | Yes | Interrupt Rating | 4 A |
| Frequency Rating | 60 Hz | Trip Range | 4 to 6 mA |
| Connection | Back and Side Wire | Amperage | 15 A |
| Number of Poles | Double Pole | Voltage | 125 V |

Environmental Conditions

95% Humidity, UL 94 V2
