



Pass and Seymour
Portable 2-Foot In-Line 15A Self-Test GFCI with Straight Blade Plug and Tri-Cord Connector, Automatic Reset
Part No. 1597TC2A



The perfect option for safely powering portable equipment, outdoors or in, when a GFCI-protected outlet is not accessible. Features a Tri-Cord Connector for plugging in multiple devices/pieces of equipment at one time. Use this 2-Foot In-Line Portable GFCI (Automatic Reset) with plugging in drills, saws, leaf blowers, pressure washers, power painters, etc. for protection against electrical shock caused by ground-faults.

Features & Benefits

- Protects against electrical shock caused by ground-fault occurrences.

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected. Open neutral relay automatically cuts power to device line conductor if the neutral wire preceding the portable GFCI becomes damaged.
- Conducts an industry-leading automatic self-test every 3 seconds. If the portable GFCI device ever fails, the red indicator light flashes to signal it should be replaced.

Automatically energizes portable GFCI for use upon plug-in and after loss of primary power.

Specifications

General Info			
Product Line	Pass & Seymour	Color	Black
Finish	Matte	Country Of Origin	China
Outlet Type	GFCI	Application Sector	Residential/Commercial
Warranty Type	1-Year Limited Warranty	Type	Straight Blade
Dimensions			
Product Width US	2.0 in	Product Weight US	1.1 lb
Product Depth US	1.75 in	Product Length US	27.75 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	943	cULus Listed	Yes
Additional Information			
RoHS Conformant	Yes		
Technical Information			
Is Tamper-Resistant	No	Amperage	15 A

Is Weather Resistant	No	Indoor/Outdoor	Outdoor
NEMA Configuration Code	5-15P, 5-15R	Voltage	125.0 V