



Pass and Seymour  
20A, 125V Watertight Straight Blade Connector, Black  
Part No. 15W33BK



Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour watertight plugs and connectors feature multiple seals to ensure protection against the environment. Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

## Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color coded sealing bushings provided for large range of cord diameters

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

## Specifications

### General Info

|                   |                             |                    |            |
|-------------------|-----------------------------|--------------------|------------|
| Product Line      | Pass & Seymour              | Color              | Black      |
| Country Of Origin | United States               | Application Sector | Commercial |
| Standard          | CSA Listed, FSUL, UL Listed |                    |            |

### Dimensions

|                  |         |                   |         |
|------------------|---------|-------------------|---------|
| Product Width US | 1.85 in | Product Length US | 2.62 in |
|------------------|---------|-------------------|---------|

### Technical Information

|                 |        |            |       |
|-----------------|--------|------------|-------|
| Phase           | Single | Connection | Cable |
| Number of Wires | 3      | Amperage   | 20 A  |

|                 |             |                          |   |
|-----------------|-------------|--------------------------|---|
| Number of Poles | Double Pole | Wire Size                | 18 - 12 AWG   |
| Voltage         | 125.0 V     | Environmental Conditions | Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized |