



Die-Cast Power Interrupting Plug with Flanged Inlet 30A 600VAC, 20A 250VAC

Features & Benefits

Quality Materials, durability, and time-tested design

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Industrial	Standard	UL498

Dimensions

Product Width US	2.87 in	Product Height US	4.59 in
------------------	---------	-------------------	---------

Technical Information

Number of Wires	4	Amperage	30 A
Number of Poles	3-Way	Wire Size	14 - 10 AWG
Voltage	600.0 V		