



Pass and Seymour
Discontinued - In Line Portable 20A GFCI, Manual Reset
Part No. 2094TL2M

Portable Ground Fault Circuit Interrupter, 20amp 125volt 2' Cord,
Manual Reset



Features & Benefits

In-line portable GFCI interrupter

Specifications

General Info

| | | | |
|-------------------|--|-------------------------|------------------------|
| Product Line | Pass & Seymour | Replaced by Part Number | 2097TL2M |
| Country Of Origin | China | Application Sector | Residential/Commercial |
| Standard | cULus, UL943, UL498, C22.2 No. 144, C22.2 No. 42, ROHS-Compliant | | |

Technical Information

| | | | |
|--------------------------|--------------------------|------------|---------------------------|
| Trip Type | Manual | Phase | Single phase installation |
| Frequency Rating | 60 Hz | Trip Range | 5+/-1 |
| Connection | Side and back wire. | Amperage | 20 A |
| Number of Poles | Double Pole | Voltage | 125 V |
| Environmental Conditions | -35C(-30F) to +66C(150F) | | |