



Pass and Seymour
Hospital Grade 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Black
Part No. 2097HGBK



Hospital-Grade 20A Self-Test Duplex GFCI

Features & Benefits

Hospital Grade	Protects children: patented shutter system helps prevent improper insertion of foreign objects meeting
GFCI self-test	National Electrical Code: Tamper-Resistant requirements

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Commercial, GFCI, Indoor, Self-Test	Application Sector	Residential/Commercial
Standard	cULus, UL Listed, FSUL	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

Interrupt Rating	4 A	Frequency Rating	60 Hz
Trip Range	5±1 mA	Connection	Back and Side Wire
Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	Voltage	125.0 V
Environmental Conditions	95% Humidity, UL 94 V2		
