



Pass and Seymour  
Discontinued - 20A 125V Hospital-Grade Tamper-Resistant Weather-Resistant Duplex GFCI Receptacle, Black  
Part No. 2097HGTRWRBK



Hospital-Grade Tamper-Resistant Weather-Resistant 15A Self-Test Duplex GFCI

## Features & Benefits

Hospital Grade GFCI self-test CH versions feature a factory broken split circuit tab allowing you to control half of the receptacle.

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	PT2097HGTRWRBK
Color	Black	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Commercial, GFCI, Outdoor, Tamper-Resistant, Weather-Resistant
Type	Outlet		

### Dimensions

Product Width US	1.73 in	Product Depth US	1.13 in
Product Height US	4.2 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Outdoor	Voltage	125.0 V