



Pass and Seymour
Portable 2-Foot In-Line GFCI with Straight Blade Plug and Connector, Manual Reset
Part No. 2097PC2M



Stay safer on any job, any project with this code-compliant 2-Foot In-Line Portable GFCI (Manual Reset). Designed for use with portable equipment (drills, saws, power painters, etc.), providing protection against electrical shock caused by ground faults.

Features & Benefits

Protects against electrical shock caused by ground-fault occurrences.

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected. Open neutral relay automatically cuts power to device line conductor if the neutral wire preceding the portable GFCI becomes damaged.

Conducts an industry-leading automatic self-test every 3 seconds. If the portable GFCI device ever fails, the red indicator light flashes to signal it should be replaced.

Requires portable GFCI to be manually set for use by pressing reset button upon plug in and after loss of primary power.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Finish	Matte	Country Of Origin	China
Outlet Type	GFCI	Application Sector	Residential/Commercial
Warranty Type	1-Year Limited Warranty	Type	Straight Blade

Dimensions

Product Width US	2.0 in	Product Weight US	1.0 lb
Product Depth US	1.75 in	Product Length US	27.75 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	943	cULus Listed	Yes
---------------------	-----	--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Is Tamper-Resistant	No	Amperage	20 A
---------------------	----	----------	------

Is Weather Resistant	No	Indoor/Outdoor	Outdoor
----------------------	----	----------------	---------

NEMA Configuration Code	5-15P, 5-15R	Voltage	125.0 V
-------------------------	--------------	---------	---------
