



Metallic Power Interrupting Plug with Rubber Cord Grips 3-Pole, 4W,
30A/600V, 20A/250VDC, 0.48-0.75 ARM

Features & Benefits

Quality Materials, durability, and time-tested design

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Industrial	Standard	UL498
Type	Plug Tail		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	PENDING
------------	-----	-----------------	---------

Technical Information

Number of Wires	4	Amperage	30 A
Number of Poles	3-Way	Wire Size	14 - 10 AWG
Voltage	600.0 V		
