

Locking Rubber Connector 15amp 125volt L5-15r



Features & Benefits

Rubber body construction stands up to impacts, oil, chemicals, heat, and weather.

Floating blades allow self-alignment with contacts and reduce stress on blades and contacts.

Neoprene grommet keeps out contaminants at cord entrance.

Terminal screws come backed out -- ready-to-wire.

Nickel-plated blades and connectors provide an extra measure of corrosion resistance.

Closure cap on watertight model forms a seal to keep out contaminants when connector is not in use.

Multiple seals between plug and connector on watertight version protects electrical connection from contaminants.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Application Sector	Industrial
Standard	UL498		

Dimensions

Product Width US	1.58 in	Product Length US	3.1 in
------------------	---------	-------------------	--------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	701645
------------	-----	-----------------	--------

Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Voltage	277.0 V		
