



Heavy-Duty Decorator Spec Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.	One-piece, brass, triple-wipe power contacts for lasting retention.
Heavy-duty compact design for easier installation and long lasting performance.	Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
Impact-resistant nylon face.	Terminal compartments isolated from each other for positive conductor containment.
All devices fit standard #26 opening wall plate.	Tri-drive terminal and mounting screws.
Auto-ground clip assures positive ground.	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor	Application Sector	Commercial
Standard	UL498, cUL CSA	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2