



Pass and Seymour  
Rubber Dust-Tight Locking Plug, Yellow  
Part No. 2877



Locking Dust-Tight Rubber Plug, 30amp 3Y600, NEMA Configuration L17-30

## Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts,oils, chemicals, heat, and weather

Quick lead assembly screws aid in a fast installation

Keyed body and cover for easy assembly and alignment

Two Screw cable clamp secures wire and provides superior strain relief

Industrial strength, brass blades and contacts resist heat rise while providing excellent conductivity

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Standard	UL Listed, CSA Listed

### Dimensions

Product Width US	2.3 in	Product Length US	2.963 in
------------------	--------	-------------------	----------

### Technical Information

Phase	Three	Number of Wires	4
Amperage	30 A	Number of Poles	3-Way
Wire Size	12 - 6 AWG	Voltage	600.0 V

---

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65,  
66, 67 (Plug & Connector only) Flammability  
UL94V0 (boxes & wiring device interiors) Operating  
Temperature -40°C (without impact) to +60°C  
continuous UV resistance All exposed material s  
are UV stabilized

---