



Locking Dust-Tight Rubber Connector, 30amp 277volt, NEMA Configuration L7-30.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts,oils, chemicals, heat, and weather

Quick lead assembly screws aid in a fast installation

Keyed body and cover for easy assembly and alignment

Two Screw cable clamp secures wire and provides superior strain relief

Industrial strength, brass blades and contacts resist heat rise while providing excellent conductivity

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Standard	UL Listed, CSA Listed

Dimensions

Product Width US	2.3 in	Product Length US	4.04 in
------------------	--------	-------------------	---------

Technical Information

Phase	Single	Number of Wires	3
Amperage	30 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	277.0 V

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65,
66, 67 (Plug & Connector only) Flammability
UL94V0 (boxes & wiring device interiors) Operating
Temperature -40°C (without impact) to +60°C
continuous UV resistance All exposed material s
are UV stabilized
