



Locking Dust-Tight Rubber Connector, 30amp 3Y600, NEMA Configuration L17-30.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather Two Screw cable clamp secures wire and provides superior strain relief

Quick lead assembly screws aid in a fast installation

Industrial strength, brass blades and contacts resist heat rise while providing excellent conductivity

Keyed body and cover for easy assembly and alignment

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	Yellow
UPC Number	785007032970
Country Of Origin	United States
Product Line	Pass & Seymour
Standard	UL Listed, CSA Listed

Technical Information

Number of Poles	3-Way
Voltage	600 V
Phase	Three
Wire Size	12 AWG min - 6 AWG max
Number of Wires	4

Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed materials are UV stabilized
--------------------------	---