



Pass and Seymour  
29W77 Watertight NEMA 4X/6P Locking Connector, Yellow  
Part No. 29W77



Locking Watertight Connector, 30amp 3Y 600volt, NEMA Configuration L17-30, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.

## Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color coded sealing bushings provided for large range of cord diameters

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

## Specifications

### General Info

|                   |                |          |                       |
|-------------------|----------------|----------|-----------------------|
| Product Line      | Pass & Seymour | Color    | Yellow                |
| Country Of Origin | United States  | Standard | UL Listed, CSA Listed |

### Dimensions

|                  |         |                   |         |
|------------------|---------|-------------------|---------|
| Product Width US | 2.35 in | Product Length US | 4.75 in |
|------------------|---------|-------------------|---------|

### Technical Information

|           |            |                 |         |
|-----------|------------|-----------------|---------|
| Phase     | Single     | Number of Wires | 4       |
| Amperage  | 30 A       | Number of Poles | 3-Way   |
| Wire Size | 12 - 6 AWG | Voltage         | 600.0 V |

---

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65,  
66, 67 (Plug & Connector only) Flammability  
UL94V0 (boxes & wiring device interiors) Operating  
Temperature -40°C (without impact) to +60°C  
continuous UV resistance All exposed material s  
are UV stabilized

---