



Pass and Seymour
20A 125/250V 14-20R Straight Blade Single Flush Receptacle, 3-Pole, 4-Wire
Part No. 3820

Straight Blade Receptacle 3-Pole 4-Wire 20A 125/250V



Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Standard	UL 498		

Dimensions

Product Depth US	1.23 in	Product Height US	2.2 in
------------------	---------	-------------------	--------

Technical Information

Connection	Non Ground	Number of Wires	4
Amperage	20 A	Number of Poles	3-Way
Wire Size	4	Voltage	125.0 V