


Hospital Grade Quad Receptacle 20A 125V



Features & Benefits

Rugged nylon face and body withstands impacts and hard use.

Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.

Shielding walls guard against live-circuit-to-ground shorts.

UL and CSA listed.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Built-in wire stripping gauge.

Heavy-duty, phosphor bronze contacts.

Split circuit break-off tabs.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 498, 1449		

Dimensions

Product Width US	4.5 in
------------------	--------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16063
------------	-----	-----------------	-------

Technical Information

Phase	3	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Voltage	125.0 V
