


## Hospital Grade Quad Receptacle 20A 125V



### Features & Benefits

- Rugged nylon face and body withstands impacts and hard use.
  - Built-in wire stripping gauge.
  - Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.
  - Heavy-duty, phosphor bronze contacts.
  - Shielding walls guard against live-circuit-to-ground shorts.
  - Split circuit break-off tabs.
  - UL and CSA listed.
  - For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 498, 1449		

#### Dimensions

Product Width US	4.5 in
------------------	--------

#### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16063
------------	-----	-----------------	-------

---

Technical Information

Phase	3	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Voltage	125.0 V

---