



Quad Receptacle 20A 125V

## Features & Benefits

Rugged nylon face and body withstands impacts and hard use.

Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.

Shielding walls guard against live-circuit-to-ground shorts.

UL and CSA listed.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Built-in wire stripping gauge.

Heavy-duty, phosphor bronze contacts.

Split circuit break-off tabs.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL498, CSA C22.2 No. 42		

### Dimensions

Product Width US	4.5 in
------------------	--------

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16063
------------	-----	-----------------	-------

---

Technical Information

Number of Wires	3	Temperature Rating	-40° - 65° C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 12 AWG	Voltage	125.0 V
Environmental Conditions	Flammability: UL94 V2 and UL94-5 VA		

---