

Turnlok® Single Receptacle 3-Wire 15A 125A



## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Standard	UL 498

### Dimensions

Product Width US	1.437 in	Product Depth US	1.0 in
Product Height US	2.25 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

Technical Information

---

Number of Wires	3	Amperage	15 A
-----------------	---	----------	------

---

Number of Poles	Double Pole	Wire Size	4
-----------------	-------------	-----------	---

---

Voltage	125.0 V
---------	---------

---