



Ten 20A outlets with t-slots. 6' (1.8m) cord. Length 48" (1.2m). Computer grade surge protection, 20 Amps.

Features & Benefits

Ten outlets. 15' (4.6m) cord. Length 48" (1.2m). 15A resettable circuit breaker. Computer grade surge protection, 15 Amps.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776052671
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Type	PIOC

Dimensions

Product Width US	48.0 in	Product Height US	1.13 in
Product Length US	1.5 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant Yes

Technical Information

Phase Single Stage Frequency Rating +35dB Hz

Connection Cord-ended Class 75

Amperage 20 A Short Circuit Rating 36000 Amps [12000 Amps L-N
12000 Amps L-G 12000 Amps
N-G]

Response Time <1 ns Mounting Type Spring Clip

Mounting Yes Type of Indicators Light

Voltage 600.0 V
