



Wiremold  
CabinetMate Plug-In Outlet Center Unit / 120V/20A/48 long/10 O/L /6' cord/Twist Lock Plug  
Part No. 4810ULBC20R-TL



Ten 20A outlets with t-slots, 6' (1.8m) cord. Length 48" (1.2m). Receptacle center-to-center 4" (101mm). 20 Amp unit with a 20A resettable circuit breaker. Units available with straight blade or Locking Plug.

## Features & Benefits

Ten 20A outlets with t-slots, 6' (1.8m) cord. Length 48" (1.2m). Receptacle center-to-center 4" (101mm). 20 Amp unit with a 20A resettable circuit breaker. Units available with straight blade or Locking Plug.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776052619
Country Of Origin	Mexico	Receptacle Type	Simplex
Number of Receptacles	10	Application Sector	Commercial
Standard	cULus Recognized: File E66421 Guide XBYS XUHT VZCA	Type	PIOC

### Dimensions

Product Width US	1.5 in	Product Length US	48.0 in
------------------	--------	-------------------	---------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

### Buy American Act Compliance

NAFTA	Yes
-------	-----

---

## Additional Information

---

RoHS Conformant      Yes

---

## Technical Information

---

Phase                      Single    Frequency Rating                      60 Hz

---

Amperage                      20 A    Enclosure Type                      Aluminum

---

Mounting Type                      Spring Clip    Voltage                      125.0 V

---

Environmental Conditions      Dry interior locations

---