


Back Box for IP67 & IP44 Non-Metallic Inlets and Receptacles. 63 amp.



## Features & Benefits

All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.

And all feature chemical-resistant thermoplastic construction.

An exclusive, hinged cord grip eliminates loose parts that get lost.

North American products come completely ready to wire, for quick, simple installation.

Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	France
--------------	----------------	-------------------	--------

### Technical Information

Data Transfer Rate	480 Mbps	Adapter Rear	RJ-45 Female, USB-A Female
--------------------	----------	--------------	----------------------------

Adapter Front	RJ-45 Female, USB-B Female
---------------	----------------------------