

Straight Blade 2-Pole 3-Wire 20A 250V Flanged Inlet



Features & Benefits

All thermoplastic construction, provides excellent impact and chemical resistance.

NEMA configuration molded on flange, easy field identification.

Available in Gray or Black.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498		

Dimensions

Product Width US	2.562 in	Product Depth US	1.655 in
------------------	----------	------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG

Voltage

250.0 V
