



Industrial Extra Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 20A 250V

Features & Benefits

One-piece brass mounting strap with integral ground.	Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
Two drive screws anchor strap to back body and face.	Exclusive patented feature, circuit label on face allows permanent circuit identification.
.036 inch thick, brass, triple-wipe power contacts for lasting retention.	Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
Impact-resistant nylon face and back body.	Oversized #10 deep tri-drive head brass terminal and ground screws.
Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.	External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
Line terminals accept #14 -- #10 AWG stranded or solid copper clad conductors.	Auto-ground clip assures positive ground.
Corrosion-resistant models have nickel-plated straps and contacts.	For covering patents, see www.legrand.us/patents .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 498, WC596		

Dimensions

Product Width US	1.625 in	Product Depth US	0.866 in
------------------	----------	------------------	----------

Product Height US	2.75 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Phase	3	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	250.0 V