



Pass and Seymour
20A 125V Watertight Straight Blade Duplex Receptacle, Yellow
Part No. 60W33DPLX



Pass and Seymour watertight receptacles feature impact-resistant Valox lids, cover plates and receptacle bodies that withstand impacts, chemical and corrosion. Ideal for the harsh environments typically found in food & beverage processing plants, petrochemical plants, marinas & shipbuilding locations, mining locations, mills and more.

Features & Benefits

Impact-resistant Valox lid, cover plate and receptacle body withstand impacts, chemicals and corrosion.

Stainless-steel hinge spring and pin ensure corrosion resistance.

For covering patents, see www.legrand.us/patents.

Wire Size: #14 - #10 AWG Copper Conductor Only

One-piece heat-treated triple-wipe brass power contacts.

Lockout/tagout capability.

Dielectric Strength, Connectors: 2000V AC if rated 300V or less, 3000V AC if rated above 300V. Plugs: 2500V AC if rated 300V or less, 3500V AC if rated above 300V.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	Country Of Origin	United States
Number of Receptacles	2	Outlet Type	Commercial, Indoor
Application Sector	Commercial	Standard	UL Listed, CSA Listed
Type	Outlet		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Temperature Rating	-40° - 60° C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	Voltage	125.0 V
