



Pass and Seymour  
15A, 125V Watertight Straight Blade, Single Receptacle, Yellow  
Part No. 60W47



Pass and Seymour Watertight Receptacles and Back Boxes mining, mills and many other locations.

## Features & Benefits

Impact-resistant Valox lid, cover plate and receptacle body withstand impacts, chemical & corrosion.

Spring-loaded flip cover provides protection when device is not in use.

Stainless-steel hinge spring and pin ensure corrosion resistance.

For Covering Patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Application Sector	Commercial
Standard	CSA Listed, FSUL, UL Listed		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

### Technical Information

Phase	Single	Connection	Cable
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 12 AWG

---

Voltage

125.0 V

Environmental Conditions

Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized

---