



Pass and Seymour
20A, 250V Watertight Straight Blade, Duplex Receptacle, Black
Part No. 60W48DPLX



Pass and Seymour watertight receptacles feature impact-resistant Valox lids, cover plates and receptacle bodies that withstand impacts, chemical and corrosion. Ideal for the harsh environments typically found in food and beverage processing plants, petrochemical plants, marinas and ship building locations, mining locations, mills and more.

Features & Benefits

Impact-resistant Valox lid, cover plate and receptacle body withstand impacts, chemicals and corrosion.

Stainless-steel hinge spring and pin ensure corrosion resistance.

For covering patents, see www.legrand.us/patents.

Spring-loaded flip cover provides protection when device is not in use.

Lockout/tagout capability.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Application Sector	Commercial
Standard	CSA Listed, FSUL, UL Listed		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	Single	Connection	Cable
Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	18 - 12 AWG

Voltage	250.0 V	Environmental Conditions	Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized
---------	---------	--------------------------	---
