



Pass and Seymour
Turnlok® 65W49DPLX Watertight Single Receptacle, Yellow
Part No. 65W49DPLX



Turnlok Watertight Duplex Receptacle, 15amp 250volt, NEMA Configuration L6-15, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|-------------------|----------------|----------|-----------------------|
| Product Line | Pass & Seymour | Color | Yellow |
| Country Of Origin | United States | Standard | UL Listed, CSA Listed |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.85 in | Product Depth US | 4.03 in |
| Product Height US | 1.85 in | | |

Technical Information

| | | | |
|-----------|-------------|-----------------|-------------|
| Phase | Single | Number of Wires | 3 |
| Amperage | 15 A | Number of Poles | Double Pole |
| Wire Size | 18 - 12 AWG | Voltage | 250.0 V |

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65,
66, 67 (Plug & Connector only) Flammability
UL94V0 (boxes & wiring device interiors) Operating
Temperature -40°C (without impact) to +60°C
continuous UV resistance All exposed material s
are UV stabilized
