


Single Pole, Three-way Combination Switch, 15 amps, 120/277 volts, Ivory. 



Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements. Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	696G
Color	Brown	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL20

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Configuration	N-0	Operating Cycles	30000
Actuator	Toggle	Connection	Side wire, non-grounding

Contact Rating	120/277 VAC, 15 Amp	Amperage	15 A
Action	{1} SP & {1} 3W	Voltage	0.433 V
Environmental Conditions	Flammability: UL94 V2		
