



Pass and Seymour  
**Turnlok® 69W75 Watertight Single Receptacle, Yellow**  
Part No. 69W75



Turnlok Watertight Single Receptacle, 30amp 3 250 volt, NEMA Configuration L15-30, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

## Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Standard	UL Listed, CSA Listed

### Dimensions

Product Width US	1.85 in	Product Depth US	4.75 in
Product Height US	1.85 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

### Technical Information

Phase	Three	Number of Wires	4
Amperage	30 A	Number of Poles	3-Way

Wire Size	12 - 6 AWG	Voltage	250.0 V
Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed materials are UV stabilized		