



Pass and Seymour  
Turnlok® 30A, 3Φ480V Watertight Single Receptacle, Black  
Part No. 69W76BK



Pass and Seymour Turnlok watertight receptacles feature impact-resistant Valox lids, cover plates and receptacle bodies that withstand impacts, chemical and corrosion. Ideal for the harsh environments typically found in food and beverage processing plants, petrochemical plants, marinas and ship building locations, mining locations, mills and more.

## Features & Benefits

Impact-resistant Valox lid, cover plate and receptacle body withstand impacts, chemicals and corrosion.

Spring-loaded flip cover provides protection when device is not in use.

Stainless-steel hinge spring and pin ensure corrosion resistance.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Dielectric Strength, Connectors: 2000V AC if rated 300V or less, 3000V AC if rated above 300V. Plugs: 2500V AC if rated 300V or less, 3500V AC if rated above 300V.

Wire Size: #14 - #10 AWG Copper Conductor Only

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	United States	Application Sector	Commercial
Standard	UL Listed, CSA Listed		

### Dimensions

Product Width US	1.85 in	Product Depth US	4.03 in
Product Height US	1.85 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

### Technical Information

Dielectric Strength	Connectors: 2000V AC if rated 300V or less, 3000V AC if rated above 300V. Plugs: 2500V AC if rated 300V or less, 3500V AC if rated above 300V.	Phase	Three
Connection	Screw terminals	Number of Wires	3
Temperature Rating	-40° - 60° C	Amperage	30 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Voltage	480.0 V	Environmental Conditions	UL94 HB