



Pass and Seymour  
**Turnlok® 69W77 Watertight Single Receptacle, Yellow**  
Part No. 69W77



Turnlok Watertight Single Receptacle, 30amp 3Y 600 volt, NEMA Configuration L17-30, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

## Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                   |                |          |                       |
|-------------------|----------------|----------|-----------------------|
| Product Line      | Pass & Seymour | Color    | Yellow                |
| Country Of Origin | United States  | Standard | UL Listed, CSA Listed |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.85 in | Product Depth US | 4.75 in |
| Product Height US | 1.85 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|            |     |
|------------|-----|
| CSA Listed | Yes |
|------------|-----|

### Technical Information

|          |        |                 |       |
|----------|--------|-----------------|-------|
| Phase    | Single | Number of Wires | 4     |
| Amperage | 30 A   | Number of Poles | 3-Way |

---

Wire Size

12 - 6 AWG

Voltage

600.0 V

---

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65,  
66, 67 (Plug & Connector only) Flammability  
UL94V0 (boxes & wiring device interiors) Operating  
Temperature -40°C (without impact) to +60°C  
continuous UV resistance All exposed material s  
are UV stabilized

---