



Wiremold
CabinetMate Plug-In Outlet Center Unit / 120V/20A/70 long/11 O/L /15' cord
Part No. 7011ULBD20R



Eleven 20A outlets with t-slots, 15' (4.6m) cord. Length 70" (1.8m). Receptacle center-to-center 6" (152mm). 20 Amp unit with a 20A resettable circuit breaker.

Features & Benefits

Eleven 20A outlets with t-slots, 15' (4.6m) cord. Length 70" (1.8m). Receptacle center-to-center 6" (152mm). 20 Amp unit with a 20A resettable circuit breaker.

Specifications

General Info

| | | | |
|-----------------------|---|--------------------|--------------|
| Product Line | Wiremold | UPC Number | 786776052589 |
| Country Of Origin | Mexico | Receptacle Type | Simplex |
| Number of Receptacles | 11 | Application Sector | Commercial |
| Standard | cULus Recognized: File E66421 Guide XBYS XUHT VZCA | Type | PIOC |

Dimensions

| | | | |
|------------------|--------|-------------------|---------|
| Product Width US | 1.5 in | Product Length US | 70.0 in |
|------------------|--------|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E66421 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Buy American Act Compliance

| | |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

Additional Information

RoHS Conformant Yes

Technical Information

Phase Single Frequency Rating 60 Hz

Amperage 20 A Enclosure Type Aluminum

Mounting Type Spring Clip Voltage 125.0 V

Environmental Conditions Dry interior locations
