




radiant Collection
radiant® Self-Grounding Tamper-Resistant Outlet, White
Part No. 885TRSW



Take a step up from the standard. This tamper-resistant duplex outlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant® for a sophisticated look. It is also designed to automatically ground to the electrical box when installed; ideal for older homes in highly-populated cities or regions where structures may not already be grounded for electrical safety. Not sure if your home's electrical wiring is grounded? Check your outlets! Outlets with slots for only two prongs are not grounded. For three-prong outlets, tester devices are available to confirm proper grounding, or you can call your local electrician for an inspection. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

- Replaces any standard outlet with ease, in as little as 10 minutes. Features durable, high-impact resistant thermoplastic construction.
- Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect. Ensures grounding for electrical safety with automatic ground clip.
- More color options available to fit any style. Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.
- Auto-Ground clip assures positive ground to metal box. Auto-Ground clip assures positive ground to metal box.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Indoor, Residential, Self-Grounding, Tamper-Resistant
Application Sector	Residential/Commercial	Standard	UL 498
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.29 in	Product Depth US	1.0 in
------------------	---------	------------------	--------

Product Height US	4.2 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Is Tamper-Resistant	Yes	Number of Gangs	1
---------------------	-----	-----------------	---

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
----------------	--------	-------------------------	-------

Mounting Type	Box	Voltage	125.0 V
---------------	-----	---------	---------

Environmental Conditions	95% (relative humidity, non-condensing)
--------------------------	---
