



Pass and Seymour
Discontinued - Wide Slide Series Dimmer, Ivory | Sub WS703TC
Part No. 906831

Slide Dimmer, 600watt Preset 3way, Ivory



Features & Benefits

Maximum ratings are for continuous full load.

RFI suppression built in.

Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.

For covering patents, see www.legrand.us/patents.

Many 1000W models fit standard Decorator plates.

Full-On bypass.

600W maximum rated dimmers can be ganged without de-rating.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	WS703PTC
Color	Ivory	Country Of Origin	Mexico
Application Sector	Residential	Standard	RoHS, CSA Listed, UL Listed

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	48758
------------	-----	-----------------	-------

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Number of Poles	3-Way	Wattage	600 W

Voltage	120.0 V	Load	Incandescent
Environmental Conditions	Humidity: Less than 95% non condensing		