

Rotary Fan Speed Control, 12amp 1pole, Ivory



Features & Benefits

Full range variable low to high speed control.

Easily ganged by removing scored heat sink fins.

Heavy-duty toroid choke for RFI suppression.

Black anodized heat sink for greater heat dispersion and enhanced appearance.

100 percent tested for symmetry for extended fan life.

Ground lead provided.

Ferrite bar coil choke for excellent RFI suppression.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	CDSC12I
Color	Ivory	Country Of Origin	Mexico

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	48758
------------	-----	-----------------	-------

Technical Information

Amperage	12 A
----------	------