



Cablofil
CabloPort Block 29" Long [943526]
 Part No. 943526



Cablo-Port is a UV and Weather resistant rubber base that creates a cushion between rooftop mounted equipment and sensitive roofing materials. Available in two styles, the Standard style is perfect for smaller loads and tight spaces and the Widebody design provides a broad base to minimize roof pressure and a larger area for glue application. Cablo-Port is also available with a wide variety of pre-mounted support options, including FAS P and Channel.

Features & Benefits

Non Penetrating Weather Resistant Bases: 100% recycled bases won't deteriorate over time. UV resistant rubber supports 1000lb/ft. Composite material accepts screws or other mechanical fasteners. Choice of two base styles -- standard or widebody.

Pre-installed Supports: Multiple support options designed to speed installation. Slotted Channel supports ladder tray, wire mesh tray and tubing. Metal supports available in 3 finishes: Pre-galvanized (PG, Standard), Hot-Dipped Galvanized (GC, Optional), and 304L Stainless Steel (S4, Optional).

Wide Variety of Support Options: Height adjustability bridges rooftop gaps, structures, or other utility pathways. Angled to adapt to any roof pitch. Multiple level for stacking cable pathways.

Extends Life of Roof: Rubber base cushions heavy metal supports. Standard or Widebody styles reduce pressure points on sensitive roofing materials. Dampens vibrations.

Improves Safety: Reflective safety strip keeps cable pathways visible on dark roofs and in low light conditions.

Green Buildings: 100% recycled rubber construction assists with building qualification for LEED credits.

Fast Shipment: Most assemblies ship in 1-3 days ARO.

Specifications

General Info

| | | | |
|--------------|--------------|-------------------|--------|
| Product Line | Cablofil | Finish | Other |
| UPC Number | 800388019119 | Country Of Origin | Canada |

Dimensions

| | | | |
|-------------------|-----------|-------------------|---------|
| Product Width US | 6.0 in | Product Weight US | 16.0 lb |
| Product Volume US | 0.4 cu ft | Product Depth US | 28.8 in |
| Product Height US | 4.0 in | | |

Buy American Act Compliance

| | |
|-----|-----|
| BAA | Yes |
|-----|-----|
