



Legrand

CABPORT w/ Stainless 6" FASP [943541]
Part No. 943541

Cablo-Port is a UV and Weather resistant rubber base that creates a cushion between rooftop mounted equipment and sensitive roofing materials. Available in two styles, the Standard style is perfect for smaller loads and tight spaces and the Widebody design provides a broad base to minimize roof pressure and a larger area for glue application. Cablo-Port is also available with a wide variety of pre-mounted support options, including FAS P and Channel.

Features & Benefits

Flat roof support: For support of tray, piping or other items on flat roofs.

Install: on any roofing material or other flat surface.

Curb style maximum load: 750 lbs. (CPP5 and CPS5 - maximum load 200 lbs.).

Widebody design: has 1,000 lbs/ft maximum load and provides 5 times the surface area to minimize roof material pressure, increase load capacity and provide over 120 square in/ft for glue application.

Two support styles: FAS Profile for wire mesh trays or 13/16" galvanized channel (14 ga.) for ladder tray, piping or other material support.

Supports are available in: one standard finish and two optional finishes.

Two rubber base designs: Standard Curb and Widebody style

Specifications

General Info

UPC Number 800388019263

Countries Of Origin United States

Product Line Cablofil

Finish Other

Buy American Act Compliance

BAA Yes