



Cablofil  
CABPORT w/ Stainless 6" FASP [943541]  
Part No. 943541

Cablo-Port is a UV and Weather resistant rubber base that creates a cushion between rooftop mounted equipment and sensitive roofing materials. Available in two styles, the Standard style is perfect for smaller loads and tight spaces and the Widebody design provides a broad base to minimize roof pressure and a larger area for glue application. Cablo-Port is also available with a wide variety of pre-mounted support options, including FAS P and Channel.

## Features & Benefits

Flat roof support: For support of tray, piping or other items on flat roofs.	Two support styles: FAS Profile for wire mesh trays or 13/16' galvanized channel (14 ga.) for ladder tray, piping or other material support.
Install: on any roofing material or other flat surface.	Supports are available in: one standard finish and two optional finishes.
Curb style maximum load: 750 lbs. (CPP5 and CPS5 - maximum load 200 lbs.).	Two rubber base designs: Standard Curb and Widebody style
Widebody design: has 1,000 lbs/ft maximum load and provides 5 times the surface area to minimize roof material pressure, increase load capacity and provide over 120 square in/ft for glue application.	

## Specifications

### General Info

Product Line	Cablofil	Finish	Other
UPC Number	800388019263	Country Of Origin	United States

### Dimensions

Product Width US	6.0 in	Product Weight US	3.0 lb
Product Volume US	0.104 cu ft	Product Depth US	6.0 in
Product Height US	5.0 in		

### Buy American Act Compliance

---

BAA

Yes

---