



Legrand
CABPORT w/ 10" GC Strut [943559]
Part No. 943559

Cabo-Port is a UV and Weather resistant rubber base that creates a cushion between rooftop mounted equipment and sensitive roofing materials. Available in two styles, the Standard style is perfect for smaller loads and tight spaces and the Widebody design provides a broad base to minimize roof pressure and a larger area for glue application. Cabo-Port is also available with a wide variety of pre-mounted support options, including FAS P and Channel.

Features & Benefits

Flat roof support: For support of tray, piping or other items on flat roofs.

Install: on any roofing material or other flat surface.

Curb style maximum load: 750 lbs. (CPP5 and CPS5 - maximum load 200 lbs.).

Widebody design: has 1,000 lbs/ft maximum load and provides 5 times the surface area to minimize roof material pressure, increase load capacity and provide over 120 square in/ft for glue application.

Two support styles: FAS Profile for wire mesh trays or 13/16" galvanized channel (14 ga.) for ladder tray, piping or other material support.

Supports are available in: one standard finish and two optional finishes.

Two rubber base designs: Standard Curb and Widebody style

Specifications

General Info

UPC Number 800388019447

Countries Of Origin Canada

Product Line Cablofil

Finish Other

Dimensions

Product Volume US 0.17 cu ft

Product Width US 6.0 in

Product Height US 4.9 in

Product Weight US 5.3 lb

Product Depth US 10.0 in

Buy American Act Compliance

BAA Yes