

## Wide Slide Series Fan Speed Control 5A



## Features & Benefits

Full range speed control.

100 percent tested for symmetry for extended fan life.

Ferrite bar coil choke for excellent RFI suppression.

Utilizes standard Decorator wall plates.

Ground lead provided.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Commercial	Standard	CSA Listed, UR Listed, UL Listed

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

### Technical Information

Connection	Pigtail Leads	Contact Rating	120VAC
Amperage	5 A	Number of Poles	Single Pole
Speed Range	Variable	Voltage	120.0 V
Environmental Conditions	Indoor Only		