



Water-resistant F compression connector for RG6/U Quad Shield Coax used by many satellite and cable TV service providers.

Features & Benefits

Seat and cut all wires at once with a squeeze of the handle

Pull Test: 55 lbs

Moisture Resistant: IPS-TP13

Available in 10 and 50 packs

Specifications

General Info

Product Line	On-Q	UPC Number	804428121824
Country Of Origin	Taiwan, Province Of China	Application Sector	Residential
Standard	RoHS		

Technical Information

Conductor Range	0.022 to 0.042 (diameter):AWG	Connection	Shell and nut are nickel-plated brass
Temperature Rating	167° F	Amperage	10 A
Environmental Conditions	0		