



Legrand

14 Foot Cat 6a Patch Cable, Gray
Part No. AC6A14GYV1

This component rated 500 MHz Cat 6a patch cable fully supports 10 Gigabit Ethernet up to 100 Meters. The snagless boot protects the tab from catching on other cables in a high density patch panel application. These pat



Features & Benefits

500MHz patch cable fully supports 10 Gigabit Ethernet speeds.

ETL verified to support the Cat 6a performance patch cable specification.

Snagless overmold prevents insertion tab from catching on other cables.

Patch cable exceeds 750 insertion cycles as specified in FCC part 68 Subpart.:

Specifications

General Info

UPC Number 804428068068

Countries Of Origin Taiwan, Province Of China

Product Line On-Q

Application Sector Residential

Standard UL, CSA, FCC, TIA/EIA-568-B.2-10 meets or exceeds Cat 6a standards, 94V-0 Flame Retardant, RoHS