



adore Collection  
EXTRA-CAP WALL PLATE, MG ADORNE FPC, MAGNESIUM  
Part No. AD3WP-MG

□

Take your contemporary remodel to the next level with the adore Brushed Stainless Mirror plate. The sleek stainless surface is surrounded by a satin nickel frame for a sophisticated finish. For use with adore Furniture Power only. Sold in multiples of ten (10) plates. Steel back plate and installation hardware are not included. All other adore wall plate colors and finishes are available as custom. View our FAQ page to learn more.

## Features & Benefits

adore Cast Metal wall plates are created with real metals. Each wall plate is hand-crafted by artisans and no two are exactly alike. These slight variations in finish and color add to the unique beauty of the adore Cast Metal offering.

Available in single, double, triple, and quad sizes to support up to four functions. Also available in 1-Gang, 3-Module sizes to support multiple functions in one electrical box, such as an outlet combined with a nightlight.

Plate easily snaps onto included mounting frame and installs in minutes with no visible screws. adore products fit into your existing electrical box, so no new wires are needed.

Pair with a classic white or contemporary magnesium switch or dimmer for a unique look.

Complete your total designer look with options like a stunning adore Accent Nightlight accessory.

Your remodel looks like a million bucks. It deserves better than an ordinary light switch. Add that last finishing touch with adore, a stunning, one-of-a-kind collection of switches, dimmers, and wall plates that will transform your walls from boring to absolutely breathtaking. It's time for a beautiful switch.

## Specifications

### General Info

Product Line	Wiremold	Replaced by Part Number	
UPC Number	786776189124	Country Of Origin	Mexico
Application Sector	Hospitality	Type	Furniture Power Center

### Listing Agencies / 3rd Party Agencies

ETL Listed	Yes
------------	-----

### Buy American Act Compliance

NAFTA	Yes
-------	-----

### Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---