



adorne Collection  
adorne® 700W Incandescent/Halogen Paddle Dimmer, Magnesium, with Microban®  
Part No. ADPD703HM4



Perfect for anywhere you'd like the combined power of on/off and dimmable lighting control. Turn lights on or off with a simple rocking motion, or slide to dim to your preferred light level. This 700W version of the paddle dimmer switch is meant for use with incandescent or halogen single fixtures and small lighting groups. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

- Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Usable in both single-pole and 3-way applications.

Microban® protection\* is effective in helping protect against degradation caused by indoor UV/light exposure.  
\*Applies only to product with "Protected with Microban" label on packaging.
- For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

For use with dimmable incadescent/halogen bulbs or fixtures that do not exceed 700W. Features smooth paddle action for turning lights on and off, plus easy slider for adjusting lights to your preferred light level.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	ADPD453LM2
Color	Magnesium	Country Of Origin	China
Features	Antimicrobial Protection	Standard	cULus
Type	Dimmer		

### Technical Information

Connection	Screw Terminals	Wattage	700 W
Voltage	120 V	Load	Halogen, Incandescent