



Perfect anywhere you'd like to turn lights on and off with the simplest touch, while also enjoying the ability to dim. Featuring a translucent glass-like face, this modern dimmer lets you control your lights by simply pressing a finger to the center circle to turn lights on/off, or use the + or - on the side to dim. Use the dimmer switch on its own to control a 0-10V light or fixture from a single location, or pair with a 3-way switch to control a single light source from two locations. Pair with the matching Touch Switch for a consistent control-style throughout a room, or your entire house.

This dimmer* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Usable in both single-pole and 3-way applications.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

For use with dimmable 0-10V bulbs or fixtures. Features intuitive touch control for switching on/off and adjusting light levels.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|--|
| Product Line | Pass & Seymour | Color | Graphite |
| Country Of Origin | China | Features | Antimicrobial Protection, Indicator Lights |
| Switch Type | Touch | Number of Switches | 1 |

| | |
|---------------|---------------------------|
| Warranty Type | Limited Lifetime Warranty |
|---------------|---------------------------|

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.77 in | Product Depth US | 1.62 in |
| Product Height US | 1.77 in | | |

Technical Information

| | | | |
|--------------------|--|-----------------|--------------------|
| Electrical Rating | 120V 10A (0-10V Fluorescent), 120V 10A (0-10V LED) | Number of Gangs | 1 |
| Bulb Compatibility | Fluorescent, LED | Number of Poles | 3-Way, Single Pole |
| Mounting Type | Box | Voltage | 0 to 10 V |
| Connection Type | Internal Pressure Plates | | |